

Eaton CH32L150D

Catalog Number: CH32L150D

CH 3/4-inch loadcenter, Standard, Main lug only, 150A, D, Copper, Ch8df-combination, ch8ds-surface, NEMA 1, Metallic, Top/bottom, CH, 32, 32, Three-wire, Single-phase, #4 AWG-300 kcmil



General specifications

Product Name	Catalog Number
Eaton CH main lug loadcenter	CH32L150D
UPC	Product Length/Depth
782113098029	29.13 in
Product Height	Product Width
3.88 in	14.31 in
Product Weight	Warranty
15 lb	Limited lifetime
Certifications	Catalog Notes
UL 67 UL 50	Suitable for use as service equipment when not more than six service disconnecting mains are provided or when not used as a lighting and appliance panelboard.

defaultTaxonomyAttributeLabel

Special features

Standard

Type

Main lug only

Amperage Rating

150 A

Bus material

Copper

Cover

Ch8df-combination, ch8ds-surface

Feed type

Top/bottom

Main circuit breaker

CH

Number of circuits

32

Number of spaces

32

Phase

Single-phase

Wire size

#4 AWG-300 kcmil

Box size

D

Enclosure

NEMA 1

Enclosure material

Metallic

Interrupt rating

25 kAIC

Number of wires

3

Resources

Brochures

Type CH Circuit Breakers and Loadcenters

Loadcenters and Circuit Breakers

Catalogs

Eaton's Volume 1—Residential and Light Commercial

Drawings

Dimensional Drawing - CH 3/4 LOADCENTER, MAIN LUG ONLY, INDOOR NEMA 1, 120/240 VAC, 1 PHASE

Installation instructions

Cutler-Hammer Type CH and BR Loadcenters - Instructions

Multimedia

AFCI Educational Video

Specifications and datasheets

Eaton Specification Sheet - CH32L150D



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)