



Powering Business Worldwide

[pe.eaton.com](http://pe.eaton.com)

## CH 3/4-inch loadcenter

CH32N200J

UPC:782113098500

### Dimensions:

- **Height:** 3.88 IN
- **Length:** 34.13 IN
- **Width:** 14.31 IN

**Notes:** Panel does not include main. Order main breaker/lug kit separately. Loadcenters are factory bonded for service entrance apps. Remove bonding strap for separate neutral & ground bars for sub-feed apps.

### Warranties:

- Limited lifetime

### Specifications:

- **Special Features:** Standard
- **Type:** Convertible
- **Amperage Rating:** 200A
- **Box Size:** J
- **Bus Material:** Copper
- **Cover:** Ch8jf-combination, ch8js-surface
- **Enclosure:** NEMA 1
- **Enclosure Material:** Metallic
- **Feed Type:** Top/bottom
- **Interrupt Rating:** 10 kAIC
- **Main Circuit Breaker:** CH
- **Main Lug Wire Size:** #4-300 kcmil
- **Number Of Circuits:** 32
- **Number Of Wires:** Three-wire
- **Phase:** Single-phase
- **Wire Size:** #2 AWG-300 kcmil

### Supporting documents:

- [Dimensional Drawing - CH 3/4 LOADCENTER, CSR CONVERTIBLE, INDOOR NEMA 1, 120/240 VAC, 1 PHASE](#)



- Type CH Circuit Breakers and Loadcenters
- Eatons Volume 1-Residential and Light Commercial
- Cutler-Hammer Type CH and BR Loadcenters - Instructions
- Eaton Specification Sheet - CH32N200J

**Certifications:**

- UL 50
- UL 67

**Product compliance:** No Data



Powering Business Worldwide

[pe.eaton.com](http://pe.eaton.com)

## CH 3/4-inch loadcenter

CH32N200J

UPC:782113098500

### Dimensions:

- **Height:** 3.88 IN
- **Length:** 34.13 IN
- **Width:** 14.31 IN

**Notes:** Panel does not include main. Order main breaker/lug kit separately. Loadcenters are factory bonded for service entrance apps. Remove bonding strap for separate neutral & ground bars for sub-feed apps.

### Warranties:

- Limited lifetime

### Specifications:

- **Special Features:** Standard
- **Type:** Convertible
- **Amperage Rating:** 200A
- **Box Size:** J
- **Bus Material:** Copper
- **Cover:** Ch8jf-combination, ch8js-surface
- **Enclosure:** NEMA 1
- **Enclosure Material:** Metallic
- **Feed Type:** Top/bottom
- **Interrupt Rating:** 10 kAIC
- **Main Circuit Breaker:** CH
- **Main Lug Wire Size:** #4-300 kcmil
- **Number Of Circuits:** 32
- **Number Of Wires:** Three-wire
- **Phase:** Single-phase
- **Wire Size:** #2 AWG-300 kcmil

### Supporting documents:

- [Dimensional Drawing - CH 3/4 LOADCENTER, CSR CONVERTIBLE, INDOOR NEMA 1, 120/240 VAC, 1 PHASE](#)



- Type CH Circuit Breakers and Loadcenters
- Eatons Volume 1-Residential and Light Commercial
- Cutler-Hammer Type CH and BR Loadcenters - Instructions
- Eaton Specification Sheet - CH32N200J

**Certifications:**

- UL 50
- UL 67

**Product compliance:** No Data

---

© 2016 Eaton. All rights reserved.