

Eaton CH42B3200R

Catalog Number: CH42B3200R

Eaton CH main breaker loadcenter, Standard, Main breaker, 200 A, L, Copper, NEMA 3R, Metallic, 10 kAIC, CC, 42 Circuits, 42 Spaces, Four-wire, Three-phase, #2/0 AWG-300 kcmil, Overhead



Photo is representative

General specifications

Product Name	Catalog Number
Eaton CH main breaker loadcenter	CH42B3200R
UPC	Product Length/Depth
782113098296	39 in
Product Height	Product Width
5.19 in	14.31 in
Product Weight	Warranty
40 lb	Limited lifetime
Certifications	Catalog Notes
UL 50 UL 67	Furnished with hub closure plates.

defaultTaxonomyAttributeLabel

Special features

Standard

Type

Main breaker

Amperage Rating

200 A

Bus material

Copper

Main circuit breaker

CC

Number of circuits

42

Number of spaces

42

Phase

Three-phase

Wire size

#2/0 AWG-300 kcmil

Feed type

Overhead

Box size

L

Enclosure

NEMA 3R

Enclosure material

Metallic

Interrupt rating

10 kAIC

Number of wires

4

Resources

Brochures

Type CH Circuit Breakers and Loadcenters

Loadcenters and Circuit Breakers

Catalogs

Eaton's Volume 1—Residential and Light Commercial

Drawings

Dimensional Drawing - CH 3/4 LOADCENTER, CC MAIN BREAKER, OUTDOOR NEMA 3R, 120/240 VAC, 3 PH

Installation instructions

Cutler-Hammer Type CH and BR Loadcenters - Instructions

Multimedia

AFCI Educational Video

Specifications and datasheets

Eaton Specification Sheet - CH42B3200R



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)