



Powering Business Worldwide

pe.eaton.com

CH 3/4-inch main loadcenter

CH42NL225K

UPC:782116109968

Dimensions:

- **Height:** 3.88 IN
- **Length:** 37 IN
- **Width:** 14.31 IN

Notes: Factory installed main lug

Warranties:

- Limited lifetime

Specifications:

- **Special Features:** Standard
- **Type:** Convertible, main lug
- **Amperage Rating:** 225A
- **Box Size:** K
- **Bus Material:** Copper
- **Enclosure:** NEMA 1
- **Enclosure Material:** Metallic
- **Main Circuit Breaker:** CH
- **Number Of Circuits:** 42
- **Number Of Wires:** Three-wire
- **Phase:** Single-phase

Supporting documents:

- [Cutler-Hammer Type CH and BR Loadcenters - Instructions](#)
- [Eatons Volume 1-Residential and Light Commercial](#)
- [Type CH Circuit Breakers and Loadcenters](#)
- [Dimensional Drawing - CH 3/4 LOADCENTER, CSR CONVERTIBLE, INDOOR NEMA 1, 120/240 VAC, 1 PHASE](#)

Certifications:

- UL 67
- UL 50



Product compliance: No Data

© 2016 Eaton. All rights reserved.



Powering Business Worldwide

pe.eaton.com

CH 3/4-inch main loadcenter

CH42NL225K

UPC:782116109968

Dimensions:

- **Height:** 3.88 IN
- **Length:** 37 IN
- **Width:** 14.31 IN

Notes: Factory installed main lug

Warranties:

- Limited lifetime

Specifications:

- **Special Features:** Standard
- **Type:** Convertible, main lug
- **Amperage Rating:** 225A
- **Box Size:** K
- **Bus Material:** Copper
- **Enclosure:** NEMA 1
- **Enclosure Material:** Metallic
- **Main Circuit Breaker:** CH
- **Number Of Circuits:** 42
- **Number Of Wires:** Three-wire
- **Phase:** Single-phase

Supporting documents:

- [Cutler-Hammer Type CH and BR Loadcenters - Instructions](#)
- [Eatons Volume 1-Residential and Light Commercial](#)
- [Type CH Circuit Breakers and Loadcenters](#)
- [Dimensional Drawing - CH 3/4 LOADCENTER, CSR CONVERTIBLE, INDOOR NEMA 1, 120/240 VAC, 1 PHASE](#)

Certifications:

- UL 67
- UL 50



Product compliance: No Data

© 2016 Eaton. All rights reserved.