

Eaton CH4L125RP

Catalog Number: CH4L125RP

Eaton CH main lug loadcenters, Standard, Main lug only, 125A, 7r, Copper, NEMA 3R, Metallic, Overhead, CH, 4, Eight-pole, 4, Three-wire, Single-phase, 120/240 V, 208 Y/120, 240 V, #14-1/0 AWG



General specifications

Product Name	Catalog Number
Eaton CH main lug loadcenter	CH4L125RP
UPC	Product Length/Depth
782114190517	13 in
Product Height	Product Width
3.69 in	11 in
Product Weight	Warranty
12 lb	Limited lifetime
Certifications	Catalog Notes
UL 50 UL 67	Ground bar kits priced separately. Suitable for use as service equipment when not more than two service disconnecting mains are provided or when not used as a lighting and appliance panelboard.

defaultTaxonomyAttributeLabel

Special features

Standard

Type

Main lug only

Amperage Rating

125 A

Bus material

Copper

Feed type

Overhead

Main circuit breaker

CH

Number of circuits

4

Number Of Poles

Eight-pole

Number of spaces

4

Phase

Single-phase

Voltage rating

120/240V, 208Y/120, 240V

Wire size

#14-1/0 AWG

Box size

7R

Enclosure

NEMA 3R

Enclosure material

Metallic

Interrupt rating

25 kAIC

Number of wires

3

Resources

Brochures

[Type CH Circuit Breakers and Loadcenters](#)

[Loadcenters and Circuit Breakers](#)

Catalogs

[Eaton's Volume 1—Residential and Light Commercial](#)

Installation instructions

[Cutler-Hammer Type CH and BR Loadcenters - Instructions](#)

Multimedia

[AFCI Educational Video](#)

Specifications and datasheets

[Eaton Specification Sheet - CH4L125RP](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)