

Eaton CH50SPAST

Catalog Number: CH50SPAST

Eaton CH 3/4 in Spa Panel, CH Spa panel-quick pro, 50 circuits, single-phase, three-wire, 50 A, #14-1/10 AWG at Cu/Al at 60/75° wire, ground fault self-test feature



Photo is representative

General specifications

Product Name	Catalog Number
Eaton CH spa panel	CH50SPAST
UPC	Product Length/Depth
786685969893	3.13 in
Product Height	Product Width
4.5 in	4.5 in
Product Weight	Warranty
7.35 lb	Limited lifetime
Certifications	Catalog Notes
Contact Manufacturer	Includes a ch250gfi breaker, factory installed, and two extra circuits for convenience. Includes Ground fault self-test feature

Product specifications

Type

Ch spa panel-quick pro

Amperage Rating

50A

Number of circuits

50

Number Of Poles

Two-pole

Phase

Single-phase

Used with

Ch spa panel

Wire size

#14-1/0 AWG Cu/Al

Box size

5R

Enclosure

NEMA 3R

Number of wires

3

Resources

Brochures

Specifications and datasheets

[Eaton Specification Sheet - CH50SPAST](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)

Eaton CH50SPAST

Catalog Number: CH50SPAST

Eaton CH 3/4 in Spa Panel, CH Spa panel-quick pro, 50 circuits, single-phase, three-wire, 50 A, #14-1/10 AWG at Cu/Al at 60/75° wire, ground fault self-test feature



Photo is representative

General specifications

Product Name

Eaton CH spa panel

UPC

786685969893

Product Height

4.5 in

Product Weight

7.35 lb

Certifications

Contact Manufacturer

Catalog Number

CH50SPAST

Product Length/Depth

3.13 in

Product Width

4.5 in

Warranty

Limited lifetime

Catalog Notes

Includes a ch250gfi breaker, factory installed, and two extra circuits for convenience. Includes Ground fault self-test feature

Product specifications

Type

Ch spa panel-quick pro

Amperage Rating

50A

Number of circuits

50

Number Of Poles

Two-pole

Phase

Single-phase

Used with

Ch spa panel

Wire size

#14-1/0 AWG Cu/Al

Box size

5R

Enclosure

NEMA 3R

Number of wires

3

Resources

Brochures

Specifications and datasheets

[Eaton Specification Sheet - CH50SPAST](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)