

# Eaton CH50SPAST

Catalog Number: CH50SPAST

Eaton CH 3/4 in Spa Panel, CH Spa panel-quick pro, 50 circuits, single-phase, three-wire, 50 A, #14-1/10 AWG at Cu/Al at 60/75° wire, ground fault self-test feature



Photo is representative

## General specifications

<b>Product Name</b>	<b>Catalog Number</b>
Eaton CH spa panel	CH50SPAST
<b>UPC</b>	<b>Product Length/Depth</b>
786685969893	3.13 in
<b>Product Height</b>	<b>Product Width</b>
4.5 in	4.5 in
<b>Product Weight</b>	<b>Warranty</b>
7.35 lb	Limited lifetime
<b>Certifications</b>	<b>Catalog Notes</b>
Contact Manufacturer	Includes a ch250gfi breaker, factory installed, and two extra circuits for convenience. Includes Ground fault self-test feature

## Product specifications

### Type

Ch spa panel-quick pro

### Amperage Rating

50A

### Number of circuits

50

### Number Of Poles

Two-pole

### Phase

Single-phase

### Used with

Ch spa panel

### Wire size

#14-1/0 AWG Cu/Al

### Box size

5R

### Enclosure

NEMA 3R

### Number of wires

3

## Resources

### Brochures

### Specifications and datasheets

[Eaton Specification Sheet - CH50SPAST](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)