

# Eaton CH8BF

Catalog Number: CH8BF

Eaton CH Combination Cover, Surface or flush applications, Combination cover, B, NEMA 1, CH, Combination, 0.75 in, CH12I125b, ch16I125b, ch12I3125b, ch14b100Ab



## General specifications

<b>Product Name</b>	<b>Catalog Number</b>
Eaton CH cover	CH8BF
<b>UPC</b>	<b>Product Length/Depth</b>
782113098852	16.8 in
<b>Product Height</b>	<b>Product Width</b>
1.1 in	14.3 in
<b>Product Weight</b>	<b>Warranty</b>
5.9 lb	Limited lifetime
<b>Certifications</b>	<b>Catalog Notes</b>
Contact Manufacturer	May be used in surface or flush applications

**Special features**

Surface or flush applications

**Type**

Cover

**Amperage Rating**

400 A

**Bus material**

Aluminum

**Mounting**

Combination

**Phase**

Three-phase

**Used with**

Ch12l125b, ch16l125b, ch12l3125b, ch14b100Ab

**Box size**

B

**Enclosure**

NEMA 1

**Interrupt rating**

10 kAIC

**Size**

3/4 in

**Catalogs**

[Eaton's Volume 1—Residential and Light Commercial](#)

**Multimedia**

[AFCI Educational Video](#)

**Specifications and datasheets**

[Eaton Specification Sheet - CH8BF](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://Eaton.com/socialmedia)