

# Eaton CH8CFM

Catalog Number: CH8CFM

Eaton Flush Mechanical Interlock Trim/Deadfront, Mechanical interlock-type a, Flush mechanical interlock trim/deadfront, C, NEMA 1, Flush, 0.75 in, CH201125c, ch241125c, ch1813125c, ch2413125c, ch22b100Ac, ch22n100Ac



## General specifications

<b>Product Name</b>	<b>Catalog Number</b>
Eaton CH cover	CH8CFM
<b>UPC</b>	<b>Product Length/Depth</b>
782113099613	22 in
<b>Product Height</b>	<b>Product Width</b>
1.1 in	15.3 in
<b>Product Weight</b>	<b>Warranty</b>
8.6 lb	Limited lifetime
<b>Certifications</b>	<b>Catalog Notes</b>
Contact Manufacturer	Interlocks two ch breakers mounted across from one another

## defaultTaxonomyAttributeLabel

### Special features

Mechanical interlock-type a

### Type

Cover

### Amperage Rating

400 A

### Bus material

Aluminum

### Mounting

Flush

### Phase

Three-phase

### Used with

Ch20I125c, ch24I125c, ch18I3125c, ch24I3125c, ch22b100Ac,  
ch22n100Ac

### Box size

C

### Enclosure

NEMA 1

### Interrupt rating

10 kAIC

### Size

3/4 in

## Resources

### Catalogs

[Eaton's Volume 1—Residential and Light Commercial](#)

### Multimedia

[AFCI Educational Video](#)

### Specifications and datasheets

[Eaton Specification Sheet - CH8CFM](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)