

# Eaton CH8KF

Catalog Number: CH8KF

Eaton CH Combination Cover, Surface or flush applications, Combination cover, K, NEMA 1, CH, Combination, 0.75 in, CH30b3150I, ch30b3200AI, ch42b3200AI, ch30b3225I, ch42b3225I, ch30h3200AI, ch42h3200AI, ch42h3225I



## General specifications

<b>Product Name</b>	<b>Catalog Number</b>
Eaton CH cover	CH8KF
<b>UPC</b>	<b>Product Length/Depth</b>
782113098975	38 in
<b>Product Height</b>	<b>Product Width</b>
1.1 in	15.3 in
<b>Product Weight</b>	<b>Warranty</b>
8.6 lb	Limited lifetime
<b>Certifications</b>	<b>Catalog Notes</b>
Contact Manufacturer	May be used in surface or flush applications

## defaultTaxonomyAttributeLabel

### Special features

Surface or flush applications

### Type

Cover

### Amperage Rating

400 A

### Bus material

Aluminum

### Mounting

Combination

### Phase

Three-phase

### Used with

Ch30b3150I, ch30b3200AI, ch42b3200AI, ch30b3225I,  
ch42b3225I, ch30h3200AI, ch42h3200AI, ch42h3225I

### Box size

K

### Enclosure

NEMA 1

### Interrupt rating

10 kAIC

### Size

3/4 in

## Resources

### Catalogs

[Eaton's Volume 1—Residential and Light Commercial](#)

### Multimedia

[AFCI Educational Video](#)

### Specifications and datasheets

[Eaton Specification Sheet - CH8KF](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://Eaton.com/socialmedia)