

Specifications

Eaton CHEC24L125E

Eaton CH surge loadcenter, Provision only, Convertible, 125 A, E, 24 Circuits, #6-4/0 AWG



Photo is representative



General specifications

PRODUCT NAME	Eaton CH surge loadcenter
CATALOG NUMBER	CHEC24L125E
UPC	782116200146
PRODUCT LENGTH/DEPTH	32 in
PRODUCT HEIGHT	3 in
PRODUCT WIDTH	10 in
PRODUCT WEIGHT	7 lb
WARRANTY	Limited lifetime
CERTIFICATIONS	UL Listed
CATALOG NOTES	Order Cover CHSUR8ES or CHSUR8EF separately. CHSPT2ULTRA and breaker not included

Product specifications	
SPECIAL FEATURES	Provision only
TYPE	Main lug only
AMPERAGE RATING	125 A
BUS MATERIAL	Aluminum
NUMBER OF CIRCUITS	32
NUMBER OF SPACES	32
PHASE	Single-phase
WIRE SIZE	#6-4/0 AWG
BOX SIZE	E
ENCLOSURE	NEMA 1
INTERRUPT RATING	25 kAIC

Resources	
CATALOGS	Residential and Light Commercial, Loadcenters and Circuit Breakers, Volume 1 Tab 1
MULTIMEDIA	AFCI Educational Video
SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - CHEC24L125E
WARRANTY GUIDES	Eaton type CH circuit breaker limited warranty June 2024

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
DATE:



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark. Follow us on social media to get the latest product and support information.
All other trademarks are property of their respective owners.

