

Eaton CHF130

Catalog Number: CHF130

Eaton CH thermal magnetic circuit breaker, Type CHF 3/4-Inch standard circuit breaker, 30 A, 10 kAIC, Single-pole, 120/240V, CHF, Trip flag, common breaker trip, (1) #14-8 AWG, (2) #14-10 AWG Cu/Al, CHF, Type CH Loadcenters



General specifications

| | |
|---|-----------------------|
| Product Name | Catalog Number |
| Eaton CH thermal magnetic circuit breaker | CHF130 |
| | UPC |
| | 786685361864 |
| Product Length/Depth | Product Height |
| 3.2 in | 2.6 in |
| Product Width | Product Weight |
| 0.7 in | 0.3 lb |
| Warranty | Compliances |
| Limited lifetime residential, 1 year commercial | HACR Rated |
| | Certifications |
| | UL 489 |

Catalog Notes

HACR Rated, Single-Pole Requires One 2/4-Inch Space, With Trip Indication.

defaultTaxonomyAttributeLabel

Type

Type CHF 3/4-Inch standard circuit breaker

Amperage Rating

30 A

Voltage rating

120/240 V

Trip Type

Trip flag

Circuit breaker type

CHF

Used with

Type CH Loadcenters

Interrupt rating

10 kAIC

Main circuit breaker

CHF

Wire size

(2) #14-10 AWG Cu/Al

(1) #14-8 AWG

Number of poles

Single-pole

Resources

Brochures

[Loadcenters and Circuit Breakers](#)

[Type CH Circuit Breakers and Loadcenters](#)

[Eaton's CHF Circuit Breaker with Trip Flag](#)

Catalogs

[Eaton's Volume 1—Residential and Light Commercial](#)

Specifications and datasheets

[Eaton Specification Sheet - CHF130](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)