

Specifications



Photo is representative



Eaton CHFEP120

Eaton CH GFCI circuit breaker, Ground fault equipment protector, Trip flag, 20 A, 10 kAIC, Single-pole, 120/240 V, CHFEP, Ground fault circuit interrupter, GFI, 30 mA

General specifications

PRODUCT NAME	Eaton CH GFCI circuit breaker
CATALOG NUMBER	CHFEP120
UPC	786685627977
PRODUCT LENGTH/DEPTH	7.25 in
PRODUCT HEIGHT	6.5 in
PRODUCT WIDTH	6.75 in
PRODUCT WEIGHT	3.33 lb
WARRANTY	Limited lifetime
CERTIFICATIONS	UL 489
CATALOG NOTES	Switching Duty Rated, HACR Rated



Powering Business Worldwide

Product specifications

TYPE	Ground fault equipment protector
SPECIAL FEATURES	Trip flag
AMPERAGE RATING	20 A
VOLTAGE RATING	120/240 V
CIRCUIT PROTECTION	Ground fault circuit interrupter
INDICATORS	GFI
PROTECTION	30 mA
INTERRUPT RATING	10 kAIC
MAIN CIRCUIT BREAKER	CHFEP
NUMBER OF POLES	Single-pole

Resources

CATALOGS	Residential and Light Commercial, Metering Products, Volume 1 Tab 4
SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - CHFEP120
WARRANTY GUIDES	Eaton type CH circuit breaker limited warranty June 2024

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc

Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Follow us on social media to get the latest product and support information.



Specifications



Photo is representative



Eaton CHFEP120

Eaton CH GFCI circuit breaker, Ground fault equipment protector, Trip flag, 20 A, 10 kAIC, Single-pole, 120/240 V, CHFEP, Ground fault circuit interrupter, GFI, 30 mA

General specifications

PRODUCT NAME	Eaton CH GFCI circuit breaker
CATALOG NUMBER	CHFEP120
UPC	786685627977
PRODUCT LENGTH/DEPTH	7.25 in
PRODUCT HEIGHT	6.5 in
PRODUCT WIDTH	6.75 in
PRODUCT WEIGHT	3.33 lb
WARRANTY	Limited lifetime
CERTIFICATIONS	UL 489
CATALOG NOTES	Switching Duty Rated, HACR Rated



Powering Business Worldwide

Product specifications

TYPE	Ground fault equipment protector
SPECIAL FEATURES	Trip flag
AMPERAGE RATING	20 A
VOLTAGE RATING	120/240 V
CIRCUIT PROTECTION	Ground fault circuit interrupter
INDICATORS	GFI
PROTECTION	30 mA
INTERRUPT RATING	10 kAIC
MAIN CIRCUIT BREAKER	CHFEP
NUMBER OF POLES	Single-pole

Resources

CATALOGS	Residential and Light Commercial, Metering Products, Volume 1 Tab 4
SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - CHFEP120
WARRANTY GUIDES	Eaton type CH circuit breaker limited warranty June 2024

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc

Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Follow us on social media to get the latest product and support information.

