

Eaton CHNSURGE

Catalog Number: CHNSURGE

Eaton Type CH circuit breaker surge protective device, Two Pole, Surge Protective Device



General specifications

Product Name	Catalog Number
Eaton Type CH plug on module surge protection device	CHNSURGE
	UPC
	786689353650
Product Length/Depth	Product Height
3.5 in	2.4 in
Product Width	Product Weight
6.1 in	0.45 lb
Certifications	
cUL Certified	
UL 1449	

Type

Type CH

Frequency rating

50/60 Hz

Interrupt rating

10 kAIC

Nominal Discharge Current

3 kA

Protection

L-N, L-L

Measured limiting voltage

600 V

Maximum continuous operating voltage

150 V L-N, 300 V L-L

Surge current

18 kA

Short-circuit rating

10 kA

Brochures

[Product Family Guide](#)[Storm season is coming. Are you prepared?](#)[Eaton Surge Module Product Aid](#)[Complete Home Protection, Publication No. BR00414002E / VCG1502](#)[Eaton Solutions, Publication No. SA00404006E / VCG1302](#)[Complete Home Protection, Publication No. FL010001EN / 3PC](#)

Installation instructions

[Surge Module IL](#)

Specifications and datasheets

[Eaton Specification Sheet - CHNSURGE](#)

Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)