

Eaton CHP20L125X2

Catalog Number: CHP20L125X2

Eaton CH main lug loadcenters, PON, CH, 125 A, X2, Copper, I, NEMA 1 indoor, Steel, 25 kAIC, 40, 20, 3, Single-phase, 120/240 V, #6-2/0 AWG



General specifications

Product Name	Catalog Number
Eaton CH main lug loadcenter	CHP20L125X2
UPC	Product Length/Depth
786689054250	21 in
Product Height	Product Width
4 in	14.3 in
Product Weight	Certifications
10.8 lb	UL 67

Catalog Notes

Purchase Size X2 Cover Separately

defaultTaxonomyAttributeLabel

Special features

PON

Type

CH

Amperage Rating

125 A

Bus material

Copper

Number of circuits

40

Number of spaces

20

Phase

Single-phase

Voltage rating

120/240 V

Box size

X2

Enclosure

NEMA 1

Enclosure material

Steel

Interrupt rating

25 kAIC

Number of wires

3

Resources

Brochures

[Loadcenters and Circuit Breakers](#)

Multimedia

[AFCI Educational Video](#)

Specifications and datasheets

[Eaton Specification Sheet - CHP20L125X2](#)

Warranty guides

[Eaton type CH circuit breaker limited warranty June 2024](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)