



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## CHP32E225X6 CH Pon Loadcnr 225A Convertible W/ Lugs 32 Spaces

Eaton Corp

Catalog Number	CHP32E225X6
Manufacturer	Eaton Corp
Description	Eaton CH 3/4-In Eaton CH Loadcenter, 225A, Convertible W/ Lugs, 32 Spaces
Weight per unit	19.0 (lbs/each)
Product Category	Single Phase Convertible Load

### Features

amperage rating	225
Cover Type	X6
interrupt rating	25
media	Yes
number of spaces	32
Phase	1
Voltage Rating	120/240 V
Wattage	Single-pole

### Dimensions and Weight

Depth	34.12
Height	3.88
Size	X6
Width	14.31

### Descriptions

Description	CH PON LOADCNTR 225A CONVERTIBLE W/ LUGS 32 SPACES
extra long description	ETN CHP32E225X6 CH PON LC, 225A, CO
Features	Eaton's CH 3/4-inch loadcenters enclose CH circuit breakers for power distribution and circuit protection in residential and light commercial applications. Also called a breaker box, electrical box or even a fuse box, the main function is to take electricity supplied by the utility and distribute it throughout the home to feed lights and receptacles. Covers are typically packaged separately and available as surface or flush mount.
Long Description	Eaton CH 3/4-in Eaton CH loadcenter, 225A, convertible w/ lugs, 32 spaces
Product Type	CH Pon LC, 225A, Conv W/ Lugs, 32SP

### Manufacturer Information

Brand	Eaton
GTIN	00786689055189
Manufacturers Part Number	CHP32E225X6
UPC	786689055189



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Taxonomies, Classifications, and Categories

Category Description ..... LOADCENTERS & COVERS

Type ..... Convertible loadcenter

## Packaging

Carton ..... 1

Weight Per each ..... 19

## Uses, Certifications, and Standards

Application ..... Residential Bldgs & Facilities - Residential Bldgs & Facilities -  
Other

standard ..... UL 50,UL 67