

Eaton CHP32N200R

Catalog Number: CHP32N200R

Eaton CH plug-on neutral loadcenter, 200A, convertible, 32 spaces, NEMA 3R



General specifications

| | |
|---------------------------------|----------------------|
| Product Name | Catalog Number |
| Eaton CH convertible loadcenter | CHP32N200R |
| UPC | Product Length/Depth |
| 786689059637 | 34.13 in |
| Product Height | Product Width |
| 5.19 in | 14.31 in |
| Product Weight | Warranty |
| 35 lb | Limited lifetime |
| Certifications | |
| UL 50 | |
| UL 67 | |

defaultTaxonomyAttributeLabel

Special features

Standard

Type

Convertible

Amperage Rating

200 A

Bus material

Copper

Feed type

Overhead

Main circuit breaker

CSR

Number of circuits

64

Number of spaces

32

Phase

Single-phase

Wire size

#2/0 AWG-300 kcmil

Box size

X6

Enclosure

NEMA 3R

Enclosure material

Metallic

Interrupt rating

10 kAIC

Number of wires

3

Resources

Brochures

Loadcenters and Circuit Breakers

Multimedia

AFCI Educational Video

Specifications and datasheets

Eaton Specification Sheet - CHP32N200R



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)