

# Eaton CHP60E225X9

Catalog Number: CHP60E225X9

Eaton CH PON 3/4-in Eaton CH loadcenter, 225A, convertible, lugs inst, 60 spaces



## General specifications

Product Name	Catalog Number
Eaton CH convertible loadcenter	CHP60E225X9
UPC	Product Length/Depth
786679189696	45 in
Product Height	Product Width
3.88 in	14.31 in
Product Weight	Warranty
25.35 lb	Limited lifetime
Certifications	Catalog Notes
UL 67	Purchase Size X9 Cover Separately
UL 50	

## Product specifications

### Type

Convertible, Main Lugs Installed

### Amperage Rating

225 A

### Bus material

Copper

### Cover

X9

### Feed type

Top/bottom

### Number of circuits

60

### Number of spaces

60

### Phase

Single-phase

### Voltage rating

120/240 V

### Box size

X9

### Enclosure

NEMA 1

### Enclosure material

Metallic

### Interrupt rating

25 kAIC

### Number of wires

3

## Resources

### Brochures

[Loadcenters and Circuit Breakers](#)

### Multimedia

[AFCI Educational Video](#)

### Specifications and datasheets

[Eaton Specification Sheet - CHP60E225X9](#)

### Warranty guides

[Eaton type CH circuit breaker limited warranty June 2024](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://Eaton.com/socialmedia)