

Eaton CHPX1AS

Catalog Number: CHPX1AS

Eaton CH Indoor Surface Cover, Surface or flush universal applications, Type CH indoor surface cover, 100 A, X1, Sandlewood, NEMA 1, CH, Surface, flush, 16 Spaces, CH - 0.75 in - Plug On Neutral, CH Breakers, 120/240 V

General specifications



Photo is representative

Product Name	Catalog Number
Eaton CH cover	CHPX1AS
UPC	Product Length/Depth
786689162306	1 in
Product Height	Product Width
18.75 in	14.31 in
Product Weight	Warranty
6.3 lb	Limited lifetime
Certifications	
Contact Manufacturer	

defaultTaxonomyAttributeLabel

Special features

Surface or flush universal applications

Type

Cover

Amperage Rating

225 A

Bus material

Aluminum

Mounting

Surface, flush

Number of spaces

16

Phase

Three-phase

Used with

CH Breakers

Voltage rating

120/240 V

Box size

X1

Color

Sandalwood

Enclosure

NEMA 1

Interrupt rating

10 kAIC

Size

CH - 3/4 in - plug on neutral

Resources

Brochures

[Loadcenters and Circuit Breakers](#)

Multimedia

[AFCI Educational Video](#)

Specifications and datasheets

[Eaton Specification Sheet - CHPX1AS](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)