

# Eaton CHPX5BF

Catalog Number: CHPX5BF

Eaton CH Indoor Combination Cover, Flush-mount applications, Type CH indoor combination cover, 125 A, X5, Sandlewood, NEMA 1, CH, Flush, 32 Spaces, CH - 0.75 in - Plug On Neutral, CH Breakers, 120/240 V

## General specifications



Photo is representative

**Product Name**  
Eaton CH cover

**Catalog Number**  
CHPX5BF

**UPC**  
786689162351

**Product Length/Depth**  
1 in

**Product Height**  
30.12 in

**Product Width**  
15.31 in

**Product Weight**  
10.2 lb

**Warranty**  
Limited lifetime

**Certifications**

**Contact Manufacturer**

## defaultTaxonomyAttributeLabel

### Special features

Flush-mount applications

### Type

Cover

### Amperage Rating

225 A

### Bus material

Aluminum

### Mounting

Flush

### Number of spaces

32

### Phase

Three-phase

### Used with

CH Breakers

### Voltage rating

120/240 V

### Box size

X5

### Color

Sandalwood

### Enclosure

NEMA 1

### Interrupt rating

10 kAIC

### Size

CH - 3/4 in - plug on neutral

## Resources

### Brochures

[Loadcenters and Circuit Breakers](#)

### Multimedia

[AFCI Educational Video](#)

### Specifications and datasheets

[Eaton Specification Sheet - CHPX5BF](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)