

Eaton CHPX6LS

Catalog Number: CHPX6LS

Eaton CH Surface Cover, Type CH surface cover, 225 A, X6, Sandlewood, 34 in, 15 in, NEMA 1, Steel, CH, Surface, Single-pole, 32 Spaces, CH - 0.75 in - Plug On Neutral, CH Breakers, 120/240 V



General specifications

Product Name	Catalog Number
Eaton CH cover	CHPX6LS
UPC	Product Length/Depth
786689162474	1 in
Product Height	Product Width
34.12 in	14.31 in
Product Weight	Warranty
11.5 lb	Limited lifetime
Certifications	
Contact Manufacturer	

defaultTaxonomyAttributeLabel

Type

Cover

Amperage Rating

225 A

Bus material

Aluminum

Mounting

Surface

Number Of Poles

Single-pole

Number of spaces

32

Phase

Three-phase

Used with

CH Breakers

Voltage rating

120/240 V

Box size

X6

Color

Sandalwood

Cover height

34

Cover width

15

Enclosure

NEMA 1

Enclosure material

Steel

Interrupt rating

10 kAIC

Size

CH - 3/4 in - plug on neutral

Resources

Brochures

[Loadcenters and Circuit Breakers](#)

Multimedia

[AFCI Educational Video](#)

Specifications and datasheets

[Eaton Specification Sheet - CHPX6LS](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)