

Eaton CHPX7BS

Catalog Number: CHPX7BS

Eaton CH Surface Cover, Surface or flush universal applications, Type CH surface cover, 225 A, X7, Sandlewood, NEMA 1, CH, Surface, flush, 42 Spaces, CH - 0.75 in - Plug On Neutral, CH Breakers, 120/240 V



General specifications

| | |
|----------------------|----------------------|
| Product Name | Catalog Number |
| Eaton CH cover | CHPX7BS |
| UPC | Product Length/Depth |
| 786689162450 | 1 in |
| Product Height | Product Width |
| 37 in | 14.31 in |
| Product Weight | Warranty |
| 12.5 lb | Limited lifetime |
| Certifications | |
| Contact Manufacturer | |

defaultTaxonomyAttributeLabel

Special features

Surface or flush universal applications

Type

Cover

Amperage Rating

225 A

Bus material

Aluminum

Mounting

Surface, flush

Number of spaces

42

Phase

Three-phase

Used with

CH Breakers

Voltage rating

120/240 V

Box size

X7

Color

Sandalwood

Enclosure

NEMA 1

Interrupt rating

10 kAIC

Size

CH - 3/4 in - plug on neutral

Resources

Brochures

[Loadcenters and Circuit Breakers](#)

Multimedia

[AFCI Educational Video](#)

Specifications and datasheets

[Eaton Specification Sheet - CHPX7BS](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)