

Eaton CHQ130

Catalog Number: CHQ130

3/4" Thermal magnetic circuit breakers, Type CHQ 3/4-Inch classified replacement breaker clamshell pack, 30 A, 10 kAIC, Single-pole, 120/240V, CHQ, (1) #14-8 AWG, (2) #14-10 AWG Cu/Al, Q30, CHQ, Type CH Loadcenters

General specifications



Product Name	Catalog Number
Eaton Classified 3/4" thermal magnetic circuit breaker	CHQ130
	UPC
	782113010847
Product Length/Depth	Product Height
2.5 in	3 in
Product Width	Product Weight
0.8 in	0.3 lb
Warranty	Certifications
Limited lifetime residential, 1 year commercial	UL 489
	Catalog Notes
	Replacement for Square D Type QO Breakers. Requires one 3/4-inch (19.1 mm) space.

defaultTaxonomyAttributeLabel

Type

Type CHQ 3/4-Inch classified replacement breaker clamshell pack

Special features

Clamshell pack

Amperage Rating

30 A

Voltage rating

120/240 V

Circuit breaker type

CH

Used with

Type CH Loadcenters

Interrupt rating

10 kAIC

Main circuit breaker

CHQ

Wire size

(2) #14-10 AWG Cu/Al

(1) #14-8 AWG

Number of poles

Single-pole

Quantity

30

Resources

Brochures

[Loadcenters and Circuit Breakers](#)

[Standard circuit breaker catalog numbers - 5651B63SH09](#)

Catalogs

[Eaton's Volume 1—Residential and Light Commercial](#)

Specifications and datasheets

[Eaton Specification Sheet - CHQ130](#)