

Specifications



Photo is representative



Eaton CHR1G7N7NS

Eaton pedestal mount metered, Pos 1: Gnd fault, Pos 2: Non-gnd fault, Pos 3: Non-gnd fault, Top, Surface, Circuits: 4, Center: NEMA 5-20R2GFI, Left: NEMA 14-50R, Right: NEMA 5-20R2GFI, Ringless

Physical Attributes

CIRCUIT BREAKER POSITION 1	Ground fault
CIRCUIT BREAKER POSITION 2	Non-ground fault
CIRCUIT BREAKER POSITION 3	Non-ground fault
FEED TYPE	Top
MOUNTING	Surface
NUMBER OF CIRCUITS	4
RECEPTACLE CENTER	NEMA 5-20R2GFI
RECEPTACLE LEFT	NEMA 14-50R
RECEPTACLE RIGHT	NEMA 5-20R2GFI
TYPE	Metered-ringless

General specifications

PRODUCT NAME	Eaton pedestal mount metered
CATALOG NUMBER	CHR1G7N7NS
UPC	782114239834
PRODUCT LENGTH/DEPTH	31.25 in
PRODUCT HEIGHT	7.75 in
PRODUCT WIDTH	10 in
PRODUCT WEIGHT	27 lb
WARRANTY	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
CERTIFICATIONS	UL 231 UL Listed file E163588

Specifications



Photo is representative



Eaton CHR1G7N7NS

Eaton pedestal mount metered, Pos 1: Gnd fault, Pos 2: Non-gnd fault, Pos 3: Non-gnd fault, Top, Surface, Circuits: 4, Center: NEMA 5-20R2GFI, Left: NEMA 14-50R, Right: NEMA 5-20R2GFI, Ringless

Physical Attributes

CIRCUIT BREAKER POSITION 1	Ground fault
CIRCUIT BREAKER POSITION 2	Non-ground fault
CIRCUIT BREAKER POSITION 3	Non-ground fault
FEED TYPE	Top
MOUNTING	Surface
NUMBER OF CIRCUITS	4
RECEPTACLE CENTER	NEMA 5-20R2GFI
RECEPTACLE LEFT	NEMA 14-50R
RECEPTACLE RIGHT	NEMA 5-20R2GFI
TYPE	Metered-ringless

General specifications

PRODUCT NAME	Eaton pedestal mount metered
CATALOG NUMBER	CHR1G7N7NS
UPC	782114239834
PRODUCT LENGTH/DEPTH	31.25 in
PRODUCT HEIGHT	7.75 in
PRODUCT WIDTH	10 in
PRODUCT WEIGHT	27 lb
WARRANTY	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
CERTIFICATIONS	UL 231 UL Listed file E163588