

Eaton CHR3G9N9NS

Catalog Number: CHR3G9N9NS

Eaton pedestal mount metered, Pos 1: Gnd fault, Pos 2: Non-gnd fault, Pos 3: Non-gnd fault, Weather and tamper resist center and right receptacle, Center: NEMA 5-20R2GFI WR TR, Left: NEMA 14-30R, Right: NEMA 5-20R2GFI WR TR, Ringless



General specifications

Product Name	Catalog Number
Eaton pedestal mount metered	CHR3G9N9NS
UPC	Product Length/Depth
786685552743	31 in
Product Height	Product Width
7.5 in	10 in
Product Weight	Warranty
30 lb	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Certifications

UL 231
UL Listed file E163588

Physical Attributes

Circuit breaker position 1

Ground fault

Circuit breaker position 2

Non-ground fault

Circuit breaker position 3

Non-ground fault

Feed type

Top

Mounting

Surface

Number of circuits

4

Receptacle center

NEMA 5-20R2GF

Receptacle left

NEMA 14-30R

Receptacle right

NEMA 5-20R2GFI

Type

Metered-ringless

Miscellaneous

Special features

Water and tamper resistant center/right receptacle

Utility approvals

IA : Alliant (IP&L and WP&L)

WI : Alliant (IP&L and WP&L)

FL : MEG (Duke Energy, Florida Power, Tampa Electric, Gulf Power, Oklahoma Gas and Electric)

IN : MEG (Duke Energy, Florida Power, Tampa Electric, Gulf Power, Oklahoma Gas and Electric)

KY : MEG (Duke Energy, Florida Power, Tampa Electric, Gulf Power, Oklahoma Gas and Electric)

NC : MEG (Duke Energy, Florida Power, Tampa Electric, Gulf Power, Oklahoma Gas and Electric)

OH : MEG (Duke Energy, Florida Power, Tampa Electric, Gulf Power, Oklahoma Gas and Electric)

SC : MEG (Duke Energy, Florida Power, Tampa Electric, Gulf Power, Oklahoma Gas and Electric)

FL : Tallahassee City Electric

Resources

Catalogs

[Eaton's Volume 1—Residential and Light Commercial](#)

Specifications and datasheets

[Eaton Specification Sheet - CHR3G9N9NS](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)