

# Specifications



Photo is representative



## Eaton CHR8N8N5NSU

Eaton pedestal mount metered, Pos 1: Non-gnd fault, Pos 2: Non-gnd fault, Pos 3: Non-gnd fault, Circuits: 4, 1, Weather resist center and left receptacle, Center: NEMA 5-20R2GFI WR, Left: NEMA 5-20R2GFI WR, Right: NEMA 6-20R2, Ringless

### General specifications

<b>PRODUCT NAME</b>	Eaton pedestal mount metered
<b>CATALOG NUMBER</b>	CHR8N8N5NSU
<b>UPC</b>	786685948430
<b>PRODUCT LENGTH/DEPTH</b>	30.875 in
<b>PRODUCT HEIGHT</b>	7.125 in
<b>PRODUCT WIDTH</b>	9.75 in
<b>PRODUCT WEIGHT</b>	30 lb
<b>WARRANTY</b>	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
<b>CERTIFICATIONS</b>	UL Listed



Powering Business Worldwide

## Physical Attributes

<b>CIRCUIT BREAKER POSITION 1</b>	Non-ground fault
<b>CIRCUIT BREAKER POSITION 2</b>	Non-ground fault
<b>CIRCUIT BREAKER POSITION 3</b>	Non-ground fault
<b>FEED TYPE</b>	BOTTOM
<b>NUMBER OF SOCKETS</b>	1
<b>RECEPTACLE CENTER</b>	5-20R2GFI WR
<b>RECEPTACLE LEFT</b>	5-20R2GFI WR
<b>RECEPTACLE RIGHT</b>	6-20R2
<b>TYPE</b>	Metered-ringless

## Resources

### SPECIFICATIONS AND DATASHEETS

[Eaton Specification Sheet - CHR8N8N5NSU](#)

### WARRANTY GUIDES

[Selling Policy 25-000 - Distribution and Control Products and Services](#)

**PROJECT NAME:**

**PROJECT NUMBER:**

**PREPARED BY:**

**DATE:**



### Eaton Corporation plc

Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Follow us on social media to get the latest product and support information.



# Specifications



Photo is representative



## Eaton CHR8N8N5NSU

Eaton pedestal mount metered, Pos 1: Non-gnd fault, Pos 2: Non-gnd fault, Pos 3: Non-gnd fault, Circuits: 4, 1, Weather resist center and left receptacle, Center: NEMA 5-20R2GFI WR, Left: NEMA 5-20R2GFI WR, Right: NEMA 6-20R2, Ringless

### General specifications

<b>PRODUCT NAME</b>	Eaton pedestal mount metered
<b>CATALOG NUMBER</b>	CHR8N8N5NSU
<b>UPC</b>	786685948430
<b>PRODUCT LENGTH/DEPTH</b>	30.875 in
<b>PRODUCT HEIGHT</b>	7.125 in
<b>PRODUCT WIDTH</b>	9.75 in
<b>PRODUCT WEIGHT</b>	30 lb
<b>WARRANTY</b>	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
<b>CERTIFICATIONS</b>	UL Listed



Powering Business Worldwide

## Physical Attributes

<b>CIRCUIT BREAKER POSITION 1</b>	Non-ground fault
<b>CIRCUIT BREAKER POSITION 2</b>	Non-ground fault
<b>CIRCUIT BREAKER POSITION 3</b>	Non-ground fault
<b>FEED TYPE</b>	BOTTOM
<b>NUMBER OF SOCKETS</b>	1
<b>RECEPTACLE CENTER</b>	5-20R2GFI WR
<b>RECEPTACLE LEFT</b>	5-20R2GFI WR
<b>RECEPTACLE RIGHT</b>	6-20R2
<b>TYPE</b>	Metered-ringless

## Resources

### SPECIFICATIONS AND DATASHEETS

[Eaton Specification Sheet - CHR8N8N5NSU](#)

### WARRANTY GUIDES

[Selling Policy 25-000 - Distribution and Control Products and Services](#)

**PROJECT NAME:**

**PROJECT NUMBER:**

**PREPARED BY:**

**DATE:**



### Eaton Corporation plc

Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Follow us on social media to get the latest product and support information.

