

Eaton CHR8N8N5NSU

Catalog Number: CHR8N8N5NSU

Eaton pedestal mount metered, Pos 1: Non-gnd fault, Pos 2: Non-gnd fault, Pos 3: Non-gnd fault, Circuits: 4, 1, Weather resist center and left receptacle, Center: NEMA 5-20R2GFI WR, Left: NEMA 5-20R2GFI WR, Right: NEMA 6-20R2, Ringless

General specifications



Photo is representative

Product Name

Eaton pedestal mount metered

Catalog Number

CHR8N8N5NSU

UPC

786685948430

Product Length/Depth

30.875 in

Product Height

7.125 in

Product Width

9.75 in

Product Weight

30 lb

Warranty

Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Certifications

UL Listed

defaultTaxonomyAttributeLabel

Type

Metered-ringless

Circuit breaker position 1

Non-ground fault

Circuit breaker position 2

Non-ground fault

Circuit breaker position 3

Non-ground fault

Receptacle center

5-20R2GFI WR

Receptacle left

5-20R2GFI WR

Receptacle right

6-20R2

Feed type

BOTTOM

Number of sockets

1

Resources

Specifications and datasheets

[Eaton Specification Sheet - CHR8N8N5NSU](#)

Warranty guides

[Selling Policy 25-000 - Distribution and Control Products and Services](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)