



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



CHR9N9NS Pop Ringless 2 5-20R2GFI Receptacles, *Eaton Corp*

Catalog Number	CHR9N9NS
Manufacturer	Eaton Corp
Description	Eaton Pedestal Mount Metered, Pos 1: Non-GND Fault, Pos 2: Non-GND Fault, Pos 3: None, Weather and Tamper Resist Center and Left Receptacle, Center: Nema 5-20R2GFI WR TR, Left: Nema 5-20R2GFI WR TR, Right: None, Ringless
Weight per unit	30.0 (lbs/each)
Product Category	Metered Power Outlet Pedestals

Features

dimensions	30.5000 IN X 10.0000 IN X 7.0000 IN
Mounting Type	Surface

Dimensions and Weight

Height	7.0000
Length	30.5000
Width	10.0000

Descriptions

Description	POP RINGLESS 2 5-20R2GFI RECEPTACLES,
extra long description	ETN CHR9N9NS POP, RINGLESS, (2) 5-2
Features	Eaton's temporary power panels provide safe, reliable power for RV and construction sites. Durable, long-lasting units are available as metered (ring or ringless) or unmetered and can be mounted at the surface, on a pedestal, or in a back-to-back configuration.
Long Description	Eaton pedestal mount metered, Pos 1: Non-gnd fault, Pos 2: Non-gnd fault, Pos 3: None, Weather and tamper resist center and left receptacle, Center: NEMA 5-20R2GFI WR TR, Left: NEMA 5-20R2GFI WR TR, Right: None, Ringless
Product Type	Pop, Ringless, (2) 5-20R2GFI Recp
Special Features	Water and tamper resistant left/center receptacle

Manufacturer Information

Brand	Eaton
GTIN	00786685409542
Manufacturers Part Number	CHR9N9NS
UPC	786685409542

Taxonomies, Classifications, and Categories

Category Description	RV Power Pedestals
Type	Pedestal mount metered



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Weight Per each	30

Uses, Certifications, and Standards

Application	Elec Assemblies, Panels & OEM - Electrical Assemblies, Panels and OEMs
Mounting	SURFACE
standard	UL 231,UL Listed file E163588