



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

1570 Lionel Drive  
79936-0000, TX El Paso  
Phone: 915-995-8443  
Fax: 915-245-2106



## CHSPT1208Y 3PH UL1449 3RD Edition- Type 1 SPD- 208/120vac *Eaton Corp*

Catalog Number	CHSPT1208Y
Manufacturer	Eaton Corp
Description	SPD CHSP Service Entrance Surge Protection, Type 1, 50KA One Time Surge Current Rating, Three-Phase, 120/208 Vac
Weight per unit	1.0 (lbs/each)
Product Category	Surge Suprsr-Prot Dev-LN Condi

### Features

Phase	3
Voltage Rating	120/208V Wye

### Dimensions and Weight

Depth	1
Height	1
Width	1

### Descriptions

Description	3PH UL1449 3RD EDITION- TYPE 1 SPD- 208/120VAC
extra long description	ETN CHSPT1-208Y 3PH UL1449 3RD ED T
Features	Eaton offers a comprehensive family of surge products for use at service entrances. These products can help protect sensitive electronics against the damaging effects of surges. Due to the evolution of electronics and microprocessors in the home, there is a continuous challenge to provide quality (clean) power for electronic loads such as appliances, computers/home office and entertainment systems. Surges caused by lightning, utility grid switching and other sources travel on current carrying conductors t
Long Description	SPD CHSP Service Entrance Surge Protection, Type 1, 50kA one time surge current rating, Three-phase, 120/208 Vac
Product Type	3PH UL1449 3RD Ed Type 1 SPD 208/120vac

### Manufacturer Information

Brand	Eaton
GTIN	00786685436852
Manufacturers Part Number	CHSPT1-208Y
UPC	786685436852

### Taxonomies, Classifications, and Categories

Category Description	SURGE SUPRESSION PRODUCTS
Type	Plug on module surge protection device



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

1570 Lionel Drive  
79936-0000, TX El Paso  
Phone: 915-995-8443  
Fax: 915-245-2106

## Packaging

Carton	1
Weight Per each	1

## Uses, Certifications, and Standards

Application	Elec Assemblies, Panels & OEM - Electrical Assemblies and OEMs - Other
standard	UL 1449