

Eaton CHSPT2SURGE

Catalog Number: CHSPT2SURGE

Eaton SPD Type 2 CHSP Service Entrance Surge Protection, 120/240V line, 150V L-N, 300V L-L MCOV, 700V L-N, 1200V L-L, 900V N-G, 700V L-G VPR, 22 kA SCCR, NEMA 4, Single-phase, 60 Hz, 5 kA nominal current discharge, 36 kA surge current

General specifications



Product Name

Eaton CHSPT2 surge protection device

Catalog Number

CHSPT2SURGE

UPC

786685971285

Product Length/Depth

7.5 in

Product Height

2 in

Product Width

5 in

Product Weight

0.9 lb

Warranty

Limited lifetime

Certifications

UL Recognized
cUL Certified
UL 1449

Catalog Notes

5kA nominal discharge current. Has
36kA one time surge current rating.

Product specifications

Type

Surge protection device

Special features

Meets or exceeds the requirements specified in IBC @2006, CBC2007, and UBC@Zone 4

Frequency rating

60 Hz

Interrupt rating

200 kAIC

Nominal Discharge Current

5 kA

Operating voltage

150V L-N, 300V L-L

Protection

700V L-N, 1200V L-L, 900V N-G, 700V L-G

Voltage rating

120/240 V

Enclosure

NEMA 4

Phase

Single-phase

Surge current

36 kA

Short-circuit rating

22000 kA

Operating temperature

-40 to 50 °C

Resources

Brochures

Product Family Guide

Ultra, Publication No. SA00414002E / VCG1503

Complete Home Protection, Publication No. BR00414002E / VCG1502

Storm season is coming. Are you prepared?

Complete Home Protection, Publication No. FL010001EN / 3PC

Eaton Solutions, Publication No. SA00404006E / VCG1302

Install sheets, CHSPT2

Catalogs

Surge Protection

Specifications and datasheets

Eaton Specification Sheet - CHSPT2SURGE

Warranty guides

Surge Protection Warranty WA00414003E



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)