



Powering Business Worldwide

[pe.eaton.com](http://pe.eaton.com)

## Eaton CHSPT type 2 surge protective device

CHSPT2ULTRA

UPC:786685436883

### Dimensions:

- Height: 2.5 IN
- Length: 7 IN
- Width: 5 IN

Weight:1.03 LB

### Warranties:

- Limited lifetime

### Specifications:

- Frequency Rating: 60 Hz
- Nominal Discharge Current: 20000 KA
- Operating Voltage: 150V L-N, 300V L-L
- Protection: 600V L-N, 1000V L-L, 800V N-G, 600V L-G
- Short Circuit Rating: 22000 KA
- Voltage Rating: 120/240V
- Enclosure: NEMA 4
- Phase: Single-phase
- Surge Current: 108 kA

### Supporting documents:

- [Mike Holmes - Type 2 Surge Products](#)
- [Eatons Volume 1-Residential and Light Commercial](#)
- [Complete Home Surge Protection](#)

### Certifications:

- cUL Certified
- UL 1449

Product compliance: No Data







Powering Business Worldwide

[pe.eaton.com](http://pe.eaton.com)

## Eaton CHSPT type 2 surge protective device

CHSPT2ULTRA

UPC:786685436883

### Dimensions:

- Height: 2.5 IN
- Length: 7 IN
- Width: 5 IN

Weight:1.03 LB

### Warranties:

- Limited lifetime

### Specifications:

- Frequency Rating: 60 Hz
- Nominal Discharge Current: 20000 KA
- Operating Voltage: 150V L-N, 300V L-L
- Protection: 600V L-N, 1000V L-L, 800V N-G, 600V L-G
- Short Circuit Rating: 22000 KA
- Voltage Rating: 120/240V
- Enclosure: NEMA 4
- Phase: Single-phase
- Surge Current: 108 kA

### Supporting documents:

- [Mike Holmes - Type 2 Surge Products](#)
- [Eatons Volume 1-Residential and Light Commercial](#)
- [Complete Home Surge Protection](#)

### Certifications:

- cUL Certified
- UL 1449

Product compliance: No Data



