

# Eaton CHT2020

Catalog Number: CHT2020

Eaton CH thermal magnetic circuit breaker, Type CHT twin breaker, 20 A, 10 kAIC, Single-pole, 120/240V, CHT, #14-8 AWG Cu/Al, CHT, Type CH Loadcenters, 50-60 Hz, Switching duty rated, HCAR rated



## General specifications

<b>Product Name</b>	<b>Catalog Number</b>
Eaton CH thermal magnetic circuit breaker	CHT2020
	<b>UPC</b>
	782113631547
<b>Product Length/Depth</b>	<b>Product Height</b>
0.9 in	2.6 in
<b>Product Width</b>	<b>Product Weight</b>
0.7 in	0.29 lb
<b>Certifications</b>	
UL 489	
UL Listed	

## defaultTaxonomyAttributeLabel

### Type

Type CHT twin breaker

### Amperage Rating

2 (20)

### Voltage rating

120/240 V

### Circuit breaker type

CH

### Frequency rating

50-60 Hz

### Used with

Type CH Loadcenters

### Rating

Switching duty rated, HCAR rated

### Interrupt rating

10 kAIC

### Main circuit breaker

CHT

### Wire size

#14-8 AWG Cu/Al

### Number of poles

Single-pole

## Resources

### Brochures

[Loadcenters and Circuit Breakers](#)

### Specifications and datasheets

[Eaton Specification Sheet - CHT2020](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)