

Eaton CHU1N7N4NS

Catalog Number: CHU1N7N4NS

Eaton pedestal mount unmetered, Unmetered, 50A, 20A, 30A, Non-ground fault, Non-ground fault, Non-ground fault, Top, Surface, Circuits: 4, NEMA 14-50R, NEMA 5-20R2GFI, NEMA TT-30R, 4, 3, 3, 125/250V, 125V, 125V



General specifications

Product Name	Catalog Number
Eaton pedestal mount unmetered	CHU1N7N4NS
UPC	Product Length/Depth
782114203828	4.3 in
Product Height	Product Width
17.1 in	9.5 in
Product Weight	Warranty
16 lb	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Certifications

UL 231
UL Listed file E163588

defaultTaxonomyAttributeLabel

Type

Unmetered

Circuit breaker position 1

Non-ground fault

Circuit breaker position 2

Non-ground fault

Circuit breaker position 3

Non-ground fault

Receptacle center

NEMA 5-20R2GFI

Receptacle left

NEMA 14-50R

Receptacle right

NEMA TT-30R

Feed type

Top

Mounting

Surface

Number of circuits

4

Resources

Catalogs

Eaton's Volume 1—Residential and Light Commercial

Drawings

Dimensional Drawing - POWER OUTLET, SURFACE MOUNT, UNMETERED

Specifications and datasheets

Eaton Specification Sheet - CHU1N7N4NS



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia