

# Eaton CHU2G2GKGS

Catalog Number: CHU2G2GKGS

Eaton pedestal mount unmetered, Unmetered, 20A, 20A, 20A, Ground fault, Ground fault, Ground fault, Top, Surface, Circuits: 4, NEMA 5-20R2 (2), NEMA 5-20R2(2) WR, NEMA 6-20R2(2) WR, 3, 3, 3, 125V, 125V, 250V



## General specifications

<b>Product Name</b>	<b>Catalog Number</b>
Eaton pedestal mount unmetered	CHU2G2GKGS
<b>UPC</b>	<b>Product Length/Depth</b>
786685948287	6.8 in
<b>Product Height</b>	<b>Product Width</b>
39.9 in	9.5 in
<b>Product Weight</b>	<b>Warranty</b>
15.8 lb	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

## Certifications

UL Listed

## defaultTaxonomyAttributeLabel

### Type

Unmetered

### Circuit breaker position 1

Ground fault

### Circuit breaker position 2

Ground fault

### Circuit breaker position 3

Ground fault

### Receptacle center

NEMA 5-20R2 WR

### Receptacle left

NEMA 5-20R2 WR

### Receptacle right

NEMA 6-20R2 WR

### Mounting

Surface

## Resources

### Specifications and datasheets

[Eaton Specification Sheet - CHU2G2GKGS](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)