



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



CHU602G2GKGSX Pop Unmetered Sur 6CKT 60A Main 20/20/20

Eaton Corp

Catalog Number	CHU602G2GKGSX
Manufacturer	Eaton Corp
Description	Eaton Pedestal Mount Unmetered, Unmetered, 60A Main, 20A, 20A, 20A, Ground Fault, Ground Fault, Ground Fault, Top, Surface, Circuits: 6, Nema 5-20R2 WR, Nema 5-20R2 WR, Nema 6-20R2 WR, 3, 3, 3, 125V, 125V, 250V
Weight per unit	16.0 (lbs/each)
Product Category	Distribution Equipment

Features

dimensions	6.8000 IN X 9.5000 IN X 7.6000 IN
------------	-----------------------------------

Dimensions and Weight

Depth	6.8000
Height	7.6000
Width	9.5000

Descriptions

Description	POP UNMETERED SUR 6CKT 60A MAIN 20/20/20
extra long description	ETN CHU602G2GKGSX POP UNMETERED SUR
Features	Eaton's temporary power panels provide safe, reliable power for RV and construction sites. Durable, long-lasting units are available as metered (ring or ringless) or unmetered and can be mounted at the surface, on a pedestal, or in a back-to-back configuration.
Long Description	Eaton pedestal mount unmetered, Unmetered, 60A Main, 20A, 20A, 20A, Ground fault, Ground fault, Ground fault, Top, Surface, Circuits: 6, NEMA 5-20R2 WR, NEMA 5-20R2 WR, NEMA 6-20R2 WR, 3, 3, 3, 125V, 125V, 250V
Product Type	Pop Unmetered Sur 6CKT 60A Main 20/20/20

Manufacturer Information

Brand	Eaton
GTIN	00786689528294
Manufacturers Part Number	CHU602G2GKGSX
UPC	786689528294

Taxonomies, Classifications, and Categories

Category Description	RV Power Pedestals
Type	Pedestal mount unmetered



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Weight Per each	16

Uses, Certifications, and Standards

Application	Elec Assemblies, Panels & OEM - Electrical Assemblies, Panels and OEMs
Mounting	SURFACE
standard	UL Listed