

# Eaton CHU6G6G5GS

Catalog Number: CHU6G6G5GS

Eaton pedestal mount unmetered, 20A, Ground fault, Top, Surface, Circuits: 4, NEMA 5-20R2, NEMA 6-20R2, 3, 125V, 250V

## General specifications



<b>Product Name</b>	<b>Catalog Number</b>
Eaton pedestal mount unmetered	CHU6G6G5GS
<b>UPC</b>	<b>Product Length/Depth</b>
782114203927	4.3 in
<b>Product Height</b>	<b>Product Width</b>
17.1 in	9.5 in
<b>Product Weight</b>	<b>Warranty</b>
16.25 lb	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

## Certifications

UL Listed file E163588  
UL 231

## Physical Attributes

### Circuit breaker position 1

Ground fault

### Circuit breaker position 2

Ground fault

### Circuit breaker position 3

Ground fault

### Feed type

Top

### Mounting

Surface

### Number of circuits

4

### Receptacle center

NEMA 5-20R2

### Receptacle left

NEMA 5-20R2

### Receptacle right

NEMA 6-20R2

### Type

Unmetered

## Resources

### Catalogs

[Eaton's Volume 1—Residential and Light Commercial](#)

### Drawings

[Dimensional Drawing - POWER OUTLET, SURFACE MOUNT, UNMETERED](#)

### Specifications and datasheets

[Eaton Specification Sheet - CHU6G6G5GS](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)