

Eaton CHU7N7N5NS

Catalog Number: CHU7N7N5NS

Eaton pedestal mount unmetered, 20A, Non-ground fault, Top, Surface, Circ: 4, NEMA 6-20R2, 3, 125V, 250V

General specifications

| | |
|--------------------------------|--|
| Product Name | Catalog Number |
| Eaton pedestal mount unmetered | CHU7N7N5NS |
| UPC | Product Length/Depth |
| 782114203941 | 18.2 in |
| Product Height | Product Width |
| 7.9 in | 10 in |
| Product Weight | Warranty |
| 16 lb | Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first. |

Certifications

UL 231
UL Listed file E163588



Physical Attributes

[Circuit breaker position 1](#)

Non-ground fault

[Circuit breaker position 2](#)

Non-ground fault

[Circuit breaker position 3](#)

Non-ground fault

[Feed type](#)

Top

[Mounting](#)

Surface

[Number of circuits](#)

4

[Receptacle center](#)

NEMA 5-20R2GFI

[Receptacle left](#)

NEMA 5-20R2GFI

[Receptacle right](#)

NEMA 6-20R2

[Type](#)

Unmetered

Resources

[Specifications and datasheets](#)

[Eaton Specification Sheet - CHU7N7N5NS](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)