

Specifications



Eaton CHU7N7NS

Eaton pedestal mount unmetered, Unmetered, 20A, 20A, None, Non-ground fault, Non-ground fault, None, Top, Surface, Circuits: 4, NEMA 5-20R2GFI, NEMA 5-20R2GFI, None, 3, 3, 0, 125V, 125V, None

General specifications

PRODUCT NAME	Eaton pedestal mount unmetered
CATALOG NUMBER	CHU7N7NS
UPC	782114203774
PRODUCT LENGTH/DEPTH	6.8 in
PRODUCT HEIGHT	39.9 in
PRODUCT WIDTH	9.5 in
PRODUCT WEIGHT	16 lb
WARRANTY	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
CERTIFICATIONS	UL 231 UL Listed file E163588



Powering Business Worldwide

Product specifications

TYPE	Unmetered
CIRCUIT BREAKER POSITION 1	Ground fault
CIRCUIT BREAKER POSITION 2	Non-ground fault
CIRCUIT BREAKER POSITION 3	None
RECEPTACLE CENTER	NEMA 5-20R2GFI
RECEPTACLE LEFT	NEMA 5-20R2GFI
RECEPTACLE RIGHT	None
FEED TYPE	Top
MOUNTING	Surface
NUMBER OF CIRCUITS	4

Resources

CATALOGS	Residential and Light Commercial, Power Pedestals, Volume 1 Tab 5
SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - CHU7N7NS

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark. Follow us on social media to get the latest product and support information.

All other trademarks are property of their respective owners.

