



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



CHU9N9NKNS Um Sur Pop 25-20R2GFI WT 16-20R2 W

Eaton Corp

Catalog Number	CHU9N9NKNS
Manufacturer	Eaton Corp
Description	Eaton Pedestal Mount, Unmetered, 20A, 20A, 20A, Non-Ground Fault, Non-Ground Fault, Non-Ground Fault, Top, Surface, Circuits: 4, Nema 5-20R2GFI WRTR, Nema 5-20R2GFI WRTR, Nema 6-20R2 WR, 3, 3, 3, 125V, 125V, 250V
Weight per unit	16.4 (lbs/each)
Product Category	Distribution Equipment

Features

dimensions	6.7000 IN X 9.5000 IN X 17.1000 IN
------------	------------------------------------

Dimensions and Weight

Depth	6.7000
Height	17.1000
Width	9.5000

Descriptions

Description	UM SUR POP 25-20R2GFI WT 16-20R2 W
extra long description	ETN CHU9N9NKNS UM SUR POP (2)5-20R2
Features	Eaton's temporary power panels provide safe, reliable power for RV and construction sites. Durable, long-lasting units are available as metered (ring or ringless) or unmetered and can be mounted at the surface, on a pedestal, or in a back-to-back configuration.
Long Description	Eaton pedestal mount, Unmetered, 20A, 20A, 20A, Non-ground fault, Non-ground fault, Non-ground fault, Top, Surface, Circuits: 4, NEMA 5-20R2GFI WRTR, NEMA 5-20R2GFI WRTR, NEMA 6-20R2 WR, 3, 3, 3, 125V, 125V, 250V
Product Type	Um Sur Pop (2)5-20R2GFI WT (1)6-20R2 W
Special Features	Pedestal Mount

Manufacturer Information

Brand	Eaton
GTIN	00786689321321
Manufacturers Part Number	CHU9N9NKNS
UPC	786689321321

Taxonomies, Classifications, and Categories

Category Description	RV Power Pedestals
Type	Pedestal mount unmetered



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Weight Per each	16.42

Uses, Certifications, and Standards

Application	Elec Assemblies, Panels & OEM - Electrical Assemblies, Panels and OEMs
Mounting	SURFACE
standard	UL 231,UL Listed file E163588