



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



CL240 Type CL BRKR 40A/2POLE 120/240V 10K-Classified 1"

Eaton Corp

| | |
|------------------|---|
| Catalog Number | CL240 |
| Manufacturer | Eaton Corp |
| Description | Standard Trip Circuit Breaker, 40 A, Common Tripping Mechanism, Plug-On, 120/240 V Ac, 3 In Overall Height, 3 In Overall Length, 2 In Overall Width |
| Weight per unit | 0.5000 (lbs/each) |
| Product Category | 2 Pole Standard Trip Plug-In |

Features

| | |
|------------|-----------------------------------|
| dimensions | 3.0000 IN X 2.0000 IN X 3.0000 IN |
| Poles | 2 |

Descriptions

| | |
|------------------------|---|
| Description | TYPE CL BRKR 40A/2POLE 120/240V 10K-CLASSIFIED 1" |
| extra long description | ETN CL240 CL bkr 40A/2Pole 120/240V |

Manufacturer Information

| | |
|------|----------------|
| GTIN | 00786676011679 |
| UPC | 786676011679 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|--------------------------------------|
| Category Description | CLASSIFIED BREAKERS |
| Type | 1" Thermal magnetic circuit breakers |

Packaging

| | |
|-----------------|-----|
| Carton | 5 |
| Package | 25 |
| Weight Per each | 0.5 |

Uses, Certifications, and Standards

| | |
|-------------|--|
| Application | Generation - Conventional Energy - Conventional EnergyOtherGeneration - Renewable Energy - Alternative EnergyDatacenters - IT Space: CI and Hyper ConvergedMarine Vessels and Equipment - Marine Vessels and Equipment - Other |
| standard | UL 489 |