



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

9707 Broadway St. Suite 100  
78217-0000, TX San Antonio  
Phone: 210-646-6950  
Fax: 210-826-1197



## CL360 Electrical Tester, Open Jaw Fork Meter, 200a *Klein Tools*

Catalog Number	CL360
Manufacturer	Klein Tools
Description	The CL360 Electrical Tester Is An Automatically Ranging True Root Mean Squared (TRMS) Digital Open Jaw Fork Meter That Measures Ac Current Via The Fork, Ac/DC Voltage, Continuity, and Resistance Via Test Leads. It Can Detect The Presence Of Voltage Via The Integrated Non-Contact Voltage (NCV) Tester. It Includes A Carrying Case, Test Leads and 2 X AAA Batteries.
Weight per unit	0.4000 (lbs/each)
Product Category	Meters, Panel Instruments

### Features

ac voltage	600V
auto-power off	Y
Capacitance	—
display	6000 Count LCD
functions	AC Current, AC/DC Voltage, Continuity, Resistance
included	Electrical Tester; Carrying Case; Instruction Manual; Straight Input Test Leads; and 2 x 1.5V AAA Batteries
Material	Plastic/Electronics
media	Yes
Overall Height	1.38" (3.5 cm)
Overall Width	2.12" (5.4 cm)
Temperature Range	—
Voltage	600V AC, 1000V DC

### Dimensions and Weight

Overall Length	8.39" (21.3 cm)
----------------	-----------------



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

9707 Broadway St. Suite 100  
78217-0000, TX San Antonio  
Phone: 210-646-6950  
Fax: 210-826-1197

## Descriptions

Description	ELECTRICAL TESTER, OPEN JAW FORK METER, 200A
extra long description	KLEIN CL360 Open Jaw Fork Meter, 20
Features	The CL360 Electrical Tester is an automatically ranging true root mean squared (TRMS) digital open jaw fork meter that measures AC current via the fork, AC/DC voltage, continuity, and resistance via test leads. It can detect the presence of voltage via the integrated non-contact voltage (NCV) tester. It includes a carrying case, test leads and 2 x AAA batteries.
Long Description	The CL360 Electrical Tester is an automatically ranging true root mean squared (TRMS) digital open jaw fork meter that measures AC current via the fork, AC/DC voltage, continuity, and resistance via test leads. It can detect the presence of voltage via the integrated non-contact voltage (NCV) tester. It includes a carrying case, test leads and 2 x AAA batteries.
Product Type	Open Jaw Fork Meter, 200A Ac
Special Features	Low Battery Indicator, Built-in Test Lead Holders, Backlit Display

## Manufacturer Information

Brand	Klein Tools
GTIN	00092644691140
Manufacturers Part Number	CL360
UPC	092644691140

## Taxonomies, Classifications, and Categories

Category Description	TEST EQUIPMENT, TESTERS AND MULTIMETERS
Type	Open Jaw Fork Current Meter

## Packaging

Carton	1
Weight	6.40 oz (180.0g)
Weight Per each	0.4

## Uses, Certifications, and Standards

Application	Measures AC Current, AC/DC Voltage, Continuity, Resistance
standard	Jaw and Housing: CATIV 600V/CATIII 1000V; Electrical: CATIII 600V/CATII 1000V