

Eaton CMB2424B200BTS

Catalog Number: CMB2424B200BTS

Eaton resi meter breaker, All-in-ones, 200A, Copper, NEMA 3R, Bottom and top, #6-350 kcm22 kAIC, #6-350 kcmCSR2200, Surface mounting, 24, Four-jaw, 1, 24, Single-phase, Ringless, CH breakers, 120/240 Vac

General specifications

Product Name	Catalog Number
Eaton residential meter breaker	CMB2424B200BTS
UPC	Product Length/Depth
782114987896	5.38 in
Product Height	Product Width
32.38 in	14.44 in
Product Weight	Warranty
45 lb	Limited lifetime
Certifications	
UL Listed	



Product specifications

Interrupt rating

10 kAIC

Utility approvals

IN : Indiana Michigan Power (IMP) (AEP East)

MI : Indiana Michigan Power (IMP) (AEP East)

OH : AEP Ohio (AEP East)

TN : Appalachian Power (AEP East)

VA : Appalachian Power (AEP East)

WV : Appalachian Power (AEP East)

FL : MEG (Duke Energy, Florida Power, Tampa Electric, Gulf Power, Oklahoma Gas and Electric)

IN : MEG (Duke Energy, Florida Power, Tampa Electric, Gulf Power, Oklahoma Gas and Electric)

KY : MEG (Duke Energy, Florida Power, Tampa Electric, Gulf Power, Oklahoma Gas and Electric)

NC : MEG (Duke Energy, Florida Power, Tampa Electric, Gulf Power, Oklahoma Gas and Electric)

OH : MEG (Duke Energy, Florida Power, Tampa Electric, Gulf Power, Oklahoma Gas and Electric)

SC : MEG (Duke Energy, Florida Power, Tampa Electric, Gulf Power, Oklahoma Gas and Electric)

Phase

Single-phase

Ground

#6-350 kcmil

Bus material

Copper

Number of jaws

Four-jaw

Main circuit breaker

CSR2200

Enclosure

NEMA 3R

Type

All-in-ones

Feed type

Top/bottom

Number of sockets

1

Resources

Catalogs

[Eaton's Volume 1—Residential and Light Commercial](#)

Drawings

[Dimensional Drawing - METER BREAKER EAST COAST STYLE](#)

Specifications and datasheets

[Technical Data Residential Meter Breakers: Type CH and BR Residential](#)

[Eaton Specification Sheet - CMB2424B200BTS](#)

Used with

Type CH breakers

Voltage rating

120/240 V

Number of circuits

24

Box size

C



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2023 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)