

Eaton CMBE4242B200TS

Catalog Number: CMBE4242B200TS

Eaton Meter Breaker EUSERC Type CH ,CSR2200N main breaker,Distribution section, 200A, 120/240V,Ring, 42 spaces, 42 circuits, 22 kAIC,Surface mounting, Box size D, Al bus,UG feed,4-jaws,1 socket, #6-250 kcmil line, #6-250 kcmil ground

General specifications



Photo is representative

Product Name	Catalog Number
Eaton meter breaker EUSERC	CMBE4242B200TS
UPC	Product Length/Depth
786685402758	5.38 in
Product Height	Product Width
34.38 in	22 in
Product Weight	Warranty
57 lb	Limited lifetime
Compliances	Certifications
EUSERC Approved	UL Listed

defaultTaxonomyAttributeLabel

Special features

Distribution section

Type

All-in-ones

Utility approvals

AZ : Arizona Public Service Company

ID : Idaho Power

OR : Idaho Power

WA : Seattle City Light

AK : Anchorage Municipal Light & Power

NV : NV Energy

AZ : Salt River Project (SRP)

MT : NorthWestern Energy

NE : NorthWestern Energy

SD : NorthWestern Energy

WY : NorthWestern Energy

AZ : Tucson Electric Power/ UniSource

AZ : Sulphur Springs Valley Electric Coop

WA : Puget Sound Energy

WA : Tacoma Public Utilities

Interrupt rating

10 kAIC

Box size

D

Enclosure

NEMA 3R

Ground

#6-250 kcmil

Voltage rating

120/240 V

Number of sockets

1

Phase

Single-phase

Used with

Type CH breakers

Number of circuits

42

Resources

Catalogs

Eaton's Volume 1—Residential and Light Commercial

Drawings

Dimensional Drawing - METER BREAKER PHOENIX STYLE

Specifications and datasheets

Eaton Specification Sheet - CMBE4242B200TS

Technical Data Residential Meter Breakers: Type CH and BR Residential

Bus material

Aluminum

Feed type

Overhead

Main circuit breaker

CSR2200N

Number of jaws

Four-jaw



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)