

**3M Fire Protection Products**  
3M™ Fire Barrier Sealant CP 25WB+



# High-Performance Fire Barrier Protection



## **Our #1 Selling Fire Barrier Sealant for Through-Penetrations**

3M™ Fire Barrier Sealant CP 25WB+ is a high performance fire barrier sealant ideal for use on walls, floors and ceilings. Utilizing powerful intumescent technology, it provides up to a 4-hour F-rating in through-penetrations. When properly installed, this one-part intumescent latex cures upon exposure to the atmosphere to help control the spread of fire, smoke and noxious gasses before, during and after exposure to a fire. Versatile 3M™ Fire Barrier Sealant CP 25WB+ meets the intent of LEED® VOC guidelines and is approved for use in more than 600 combined UL and Intertek listings for the most demanding firestop requirements.



# 3M™ Fire Barrier Sealant CP 25WB+

Effective and easy to install, 3M™ Fire Barrier Sealant CP 25WB+ is part of a family of 3M Fire Protection Products that offers affordable, long-lasting solutions for a variety of commercial, industrial and residential applications—brought to you by 3M, the #1 brand preferred by firestop contractors.

## Features and Benefits

- Versatile for use in multiple firestopping applications
- Listed systems for ratings up to 4 hours
- Water-based and paintable
- More than 600 UL and Intertek listings
- Easy to identify red color
- Easy to apply
- Meets the intent of LEED® VOC guidelines\*
- Minimizes noise transfer—STC-Rating of 54 when tested with STC 54-rated wall assembly

## Applications

- HVAC Ducts and Vents
- Metal Pipe
- Plastic Pipe\*\*
- Blank Openings
- Cable Trays
- Insulated Pipe
- Pipe and Cable Through-Penetrations
- Busways
- Construction Joints
- Combos
- Concrete Floors
- Static Construction Joints

\*Helps reduce the quality of indoor air contaminants that may be odorous, irritating and harmful to the comfort and well-being of the installers and occupants. <250 g/L VOC contents (less H<sub>2</sub>O and exempt solvents).

\*\*Check UL directory. Not approved for use with CPVC pipes made using Noveon® resins.



## Specifications

3M™ Fire Barrier Sealant CP 25WB+ shall be a one-component, ready-to-use, gun-grade, latex-based intumescent firestop sealant capable of expanding a minimum of 3 times its dried volume when exposed to temperatures above 1000°F (538°C). The material shall be thixotropic and shall be applicable to overhead, vertical and horizontal firestops. The sealant shall be listed by independent test agencies such as UL, Intertek or FM. 3M™ Fire Barrier Sealant CP 25WB+ shall be tested up to 4 hours in accordance with the criteria of ASTM E 814 (UL 1479) Standard Test Method for Fire Tests of Penetration Firestop Systems, ASTM E 1966 (UL 2079) Standard Test Method for Fire Resistive Joint Systems and CAN/ULC S115 Standard Method of Fire Tests of Firestop Systems. 3M™ Fire Barrier Sealant CP 25WB+ meets the requirements of the IBC, IRC, IFC, IPC, IMC, NFPA 5000, NEC (NFPA 70) and NFPA 101.

## Ordering Information

Product	Size	UPC	Units/Box	3M Stock Number
3M™ Fire Barrier Sealant CP 25WB+	10.1 fl. oz. Cartridge	000-51115-11638-4	12	98040054565
	27 fl. oz. Cartridge	000-51115-11641-4	6	98040053823
	20 fl. oz. Sausage	000-51115-11642-1	10	98040053831
	2 Gallon Pail	000-51115-11639-1	1	98040053807
	5 Gallon Pail	000-51115-11640-7	1	98040053815

LISTED

Intertek

FIRESTOP SYSTEMS  
SEE INTERTEK DIRECTORY

LISTED

ULC

LISTED

FILL, VOID OR CAVITY MATERIALS  
90G9

SUBJECT TO THE CONDITIONS OF APPROVAL  
AS A WALL & FLOOR PENETRATION  
FIRESTOP WHEN INSTALLED AS DESCRIBED  
IN THE CURRENT EDITION OF THE FMRC  
APPROVAL GUIDE

ULC

CLASSIFIED

UL

FILL, VOID OR CAVITY MATERIAL  
FOR USE IN THROUGH-PENETRATION  
FIRESTOP SYSTEMS  
SEE UL FIRE RESISTANCE DIRECTORY  
90G9



## Building and Commercial Services Division

3M Center  
Building 223-2N-21  
St. Paul, MN 55144-1000  
800-328-1687  
www.3M.com/firestop  
www.3M.com/fireproof

**Warranty and Limited Remedy:** Warranty and Limited Remedy: 3M warrants that each 3M Fire Protection Product will be free from defects in material and manufacture for 90 days from the date of purchase from 3M's authorized distributor. 3M MAKES NO OTHER EXPRESS OR IMPLIED WARRANTIES, INCLUDING ANY IMPLIED WARRANTY OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE. If a 3M product does not conform to this warranty, the sole and exclusive remedy is, at 3M's option, replacement of the 3M product or refund of the purchase price. **Limitation of Liability:** Except where prohibited by law, 3M will not be liable for any loss or damage arising from the 3M product, whether direct, indirect, special, incidental or consequential, regardless of the legal theory asserted.

© 3M 2011. All rights reserved.  
Printed in U.S.A. 98-0213-4638-6

Please recycle.

3M is a trademark of 3M. All other trademarks are the property of their respective owners.