

# Eaton CPP516

Catalog Number: CPP516

Eaton Crouse-Hinds series Arktite CPP plug, 20A, 0.312-0.625" cable diameter, Two-wire, three-pole, Brass contacts, 60 Hz, Style 2, 1 HP, Copper-free aluminum, Factory sealed, Delayed action circuit breaking, 125-250 Vac/18 Vdc

## General specifications



Product Name	Catalog Number
Eaton Crouse-Hinds series Arktite CPP plug	CPP516
	UPC
	782274175102
Product Length/Depth	Product Height
8.38 in	1.75 in
Product Width	Product Weight
1.75 in	0.8 lb

## Certifications and compliances

### Area classification

Hazardous/Classified Locations

### Standards type

NEC/CEC

### NEC hazardous rating

Class I, Division 1

Class I, Division 2

## Product specifications

### Grounding style

Style 2

### Amperage Rating

20A

### Configuration

Two-wire, three-pole

### Cable diameter

0.312-0.625 in

### Voltage rating

125-250 Vac/18 Vdc

### Horsepower

1 hp

### Frequency rating

60 Hz

### Material

Copper-free aluminum

### Contact material

Brass

### Special features

Factory sealed

### Type

Delayed action circuit breaking

## Resources

### Catalogs

[Arktite CPS, CPP and CPR Explosionproof Receptacles and Plugs catalog page](#)

### Certification reports

[Arktite CPS, CPP, CPR Explosionproof Receptacles, Plugs and Connectors Canadian certification](#)

[Arktite CPS, CPP, CPR Explosionproof Receptacles, Plugs and Connectors UL certification](#)

### Installation instructions

[IF 285 - CPP Plugs](#)

Specifications and datasheets

Eaton Specification Sheet - CPP516

---



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)