



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



CPR27 2-1/2" Rigid Coupling Threadless

Crouse-Hinds

Catalog Number	CPR27
Manufacturer	Crouse-Hinds
Description	Eaton Crouse-Hinds Series CPR Compression Coupling, Rigid/Imc, Malleable Iron, Compression Type, 2-1/2"
Weight per unit	3.6 (lbs/each)
Product Category	Rigid Conduit Fittings - Steel

Features

dimensions	4.5000 IN X 3.7500 IN X 3.7600 IN
Material	Malleable Iron

Descriptions

Description	2-1/2" RIGID COUPLING THREADLESS
extra long description	MIDWEST CPR27 2 1/2 RGD CMP CPL
Features	Crouse-Hinds series rigid/IMC connectors, couplings and combination couplings are used to join used to join rigid/IMC conduit to a box or enclosure, or to couple two ends of conduit together. Our rigid/IMC connectors and couplings are available in set screw type and compression type, in both insulated and non-insulated versions. They are available in a variety of materials to suit customer preferences, including malleable iron, steel, zinc die cast, aluminum, stainless steel and hot dip galvanized mallea
Long Description	Eaton Crouse-Hinds series CPR compression coupling, Rigid/IMC, Malleable iron, Compression type, 2-1/2"
Product Type	2 1/2 RGD CMP CPL
Special Features	Concrete Tight

Manufacturer Information

Brand	Eaton
GTIN	00784564122278
Manufacturers Part Number	CPR27
UPC	784564122278

Taxonomies, Classifications, and Categories

Category Description	Watertight Hub, 3-PIECE COUPLINGS, THREADLESS COUPLINGS AND THREADLESS CONNECTOR
Type	Compression coupling

Packaging

Carton	2
Weight Per each	3.6



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application

Commercial / Institutional Buildings / Structures - Commercial /
Institutional Buildings / Structures - Other

standard

UL 514B, CUL