



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



CRC6044BC 60A 4W 4P Pwrmate Connect *Crouse-Hinds*

Catalog Number	CRC6044BC
Manufacturer	Crouse-Hinds
Description	Eaton Crouse-Hinds Series Powermate CRC Connector, 60A, 0.440-1.375", Four-Wire, Four-Pole, Style 1, Copper-Free Aluminum, 600 Vac/250 VDC
Weight per unit	1.0 (lbs/each)
Product Category	Pin & Sleeve Devices

Features

dimensions	8.3000 IN X 2.3100 IN X 2.3100 IN
Material	Nickel-Plated Brass Mounting Base

Descriptions

Description	60A 4W 4P PWRMATE CONNECT
extra long description	CRS-H CRC6044BC CONNECT PWRMT 60A 4
Features	The Crouse-Hinds series PowerMate offering supports modularity of drilling rig systems by providing safe and reliable power connections for rigging up and rigging down equipment quickly and efficiently. PowerMate plugs, receptacles and connectors are used on SCR/VFD houses to provide power to rig equipment such as shakers, agitators, lighting circuits, mud pumps, motors, etc. This offering is the ideal rig power connection solution providing longer product life, reduced maintenance, enhanced safety and e
Long Description	Eaton Crouse-Hinds series PowerMate CRC connector, 60A, 0.440-1.375", Four-wire, four-pole, Style 1, Copper-free aluminum, 600 Vac/250 Vdc
Product Type	Connect PWRMT 60A 4W4P .39 to 1.375
Special Features	Material Thermo-Plastic, DIN Rail Mount

Manufacturer Information

Brand	EATON CROUSE-HINDS SERIES
GTIN	00662276276574
Manufacturers Part Number	CRC6044BC
UPC	662276276574

Taxonomies, Classifications, and Categories

Category Description	Pin & Sleeve Devices
Type	CONNECTOR

Packaging

Carton	1
Weight Per each	1



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application	Ind Facilities & Factories - Facility: Power Distribution and Control
environmental conditions	-40 To 60 Deg C
standard	CSA (CANADA AND US)