

Specifications



Eaton CS115GY

Eaton commercial grade toggle switch, #14-10 AWG, 15A, Commercial, Flush, 120/277V, Side wire, Screw, Gray, Load type: Motor Control, Fan, LED, Incandescent, ELV, MLV, CFL, Fluorescent, Halogen, Single-Pole, Single-Pole, Brass, PVC

General specifications

PRODUCT NAME	Eaton commercial grade toggle switch
CATALOG NUMBER	CS115GY
UPC	032664487484
PRODUCT LENGTH/DEPTH	1.3 in
PRODUCT HEIGHT	4.2 in
PRODUCT WIDTH	0.902 in
PRODUCT WEIGHT	0.11 lb
CERTIFICATIONS	cULus Listed NOM Federal Specification Classification 6241 05
PRODUCT TYPE	Commercial grade toggle switch



Powering Business Worldwide

Product specifications

TYPE Toggle switch

AMPERAGE RATING 15A

VOLTAGE RATING 120/277 V

NUMBER OF POLES Single-pole

APPLICATION Commercial

WIRING METHOD Side wire

SWITCH TYPE Single-pole

MOUNTING METHOD Flush

CONNECTOR TYPE Screw

LOAD TYPE HAL
INC
CFL
FLR
LED
ELV
MLV
Fan
Motor Control

MATERIAL PVC

ALLOWABLE WIRE SIZE #14-10 AWG

TERMINAL ENCLOSURE MATERIAL Brass

COLOR Gray

Resources

SPECIFICATIONS AND DATASHEETS [Eaton Specification Sheet - CS115GY](#)
[Commercial specification grade switches spec sheet](#)

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2026 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

