

Commercial Specification Grade Switch, White

CS20AC1W



Commercial single pole switch in white, with side wire, is made with high strength thermoplastic polycarbonate toggle which resists breaking and chipping under heavy abuse. Its one-piece brass alloy contact arm allows for reliable electrical performance. Also, the one-piece steel strap with integral ground is plated for corrosion resistance. The heavy-duty toggle bumpers allow for a smooth and quiet operation. 20amp 120/277volt.

features & benefits

- Back body made of glass-reinforced nylon. Locking support provides resistance to face and back body separation.
- Available with side wire or external screw-pressure-plate back and side wire models capable of accepting #14 - #10 AWG copper or copper-clad wire.
- Cam designed for fast make with positive break action to minimize arcing and prolong switch life.
- Oversized silver alloy contacts for longer dependable switch life.
- Tri-drive terminal and mounting screws.



specifications

General Info

Color: White
Type: Side Wire
Duty: Heavy Duty
Number Of Poles: 1

Listing Agencies/Third Party Information

CSA Listing Info: C22.2 111

CSA Standard: Yes
Federal Spec: Yes
Fed Spec Number: WS896
UL Listing No: UL20
UL Standard: Yes
UN SPS C: 39121507

Dimensions

Depth U S: 1.073"
Height U S: 3.281"
Width U S: 1.320"

Technical Information

Amps: 20 Amp
Volts: 120/277VAC
Volts A C: 120/277
Grade Type: Commercial

Buy American Act Compliance

Country of Origin: MEXICO
Buy American Act Status: Trade Agreement Act Compliant