



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## **CS20AC3W 20A 120/277VAC S Wire Comm 3W SW W** *Pass & Seymour/Legrand*

Catalog Number	CS20AC3W
Manufacturer	Pass & Seymour/Legrand
Description	Toggle Switch, 3 Poles, 3 Ways, 20 A, 120/277 V Ac, Nylon Material, Silver Cadmium Oxide Contact Material, White, Grounding Connection, Wall Mount, 1.320 (L) X 1.073 (W) X 3.281 (H) In, -40 °C Operating Temperature, +115 °C Operating Temperature, 0.18 LB
Weight per unit	0.1820 (lbs/each)
Product Category	Gen Purpose Switches

### **Features**

action	Three pole
amperage rating	20
connection	Side Wire or external screw-pressure plate
Contact Configuration	One piece brass alloy contact arm
Contact Rating	Oversized silver alloy contacts
Degree of Protection	1500V Dielectric Withstand Voltage
indoor/outdoor	Indoor
insulation	False
media	Yes
Poles	3-way
Switch Type	Toggle
Voltage	120/277 V

### **Material, Color, and Finish**

Finish	Matte
--------	-------

### **Dimensions and Weight**

Size	3.3 in
------	--------

### **Descriptions**

Description	20A 120/277VAC S WIRE COMM 3W SW W
extra long description	P&S CS20AC3W 20A 120/277VAC S WIRE

### **Manufacturer Information**

Brand	Pass and Seymour
GTIN	00785007126556
Manufacturers Part Number	CS20AC3W
UPC	785007126556

### **Taxonomies, Classifications, and Categories**

Category Description	Commercial switches
Type	SWITCH



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Trade Size

Amperage ..... 20.0

## Packaging

Carton ..... 10

Package ..... 50

Weight Per each ..... 0.182

## Uses, Certifications, and Standards

Application ..... Commercial

Enclosure ..... Nylon

Mounting ..... WALL

standard ..... CULUS, FEDSPEC, UL Listed E140597, Standard UL20, FedSpec  
WS896, Flammability Rating UL94 V2